

TECHNICAL BULLETIN

EPOXIOHM EO-32 ELECTRICALLY CONDUCTIVE EPOXY ADHESIVE

EO-32 is pure silver filled, two components epoxy adhesive. It has smooth creamy consistency with long work life at room temperature. It can cure at low temperature as well as rapid cure at higher temperature for high volume applications.

It can be used for microelectronics and chip bonding in optoelectric applications. It can be applied by silk screening, transfer printing, automatic dispensing or hand probe.

TYPICAL HANDLING PROPERTIES:

Mix ratio by weight (A: B)	100:2	
Mix Viscosity @ 25°C, cps	40,000-50,000	
(Cone & Plate viscometer, spindle-51, 100 rpm)		
Work Life (25 grams), days	>2 days	
Shelf life:		
Two Parts Kit @ 25°C	1 year	
Frozen @ -40°C	1 year	

Recommended Cure- (Bondline curing temperature)

USE ANY OF THE BELOW CURE SCHEDULE

15 minutes @ 150°C 30 minutes @ 120°C 2-3 hours @ 80-90°C

TYPICAL CURED PROPERTIES:

(Tested at 25°C unless otherwise indicated)

Color	Silver	
Specific Gravity	3.9	
Hardness, Shore D	90	
Lap Shear Strength to Aluminum, psi	2100	
Volume Resistivity, ohm-cm	< 0.0003	
Thermal Conductivity, W/mK	4.2	
Glass Transition Temperature, °C	117	
Service Temperature, °C	-55 to 200	
Coefficient of Thermal Expansion, ppm/°C		
Below Tg	42	
Above Tg	180	

INSTRUCTIONS FOR USE:

- 1. Mix each component thoroughly before use.
- 2. Weigh 10 grams of PART-A to 0.2 grams (7-8 drops) of Part B.
- Mix until uniform. Scrape the sides and bottom of container repeatedly during mixing.
- 4. Apply to clean bonding surfaces and cure as recommended to achieve the desired properties. Typical cured properties were determined using recommended cure schedule. Some difference in properties may occur with the alternate or other cure schedules.

Thaw premixed & frozen adhesive at room temperature for 5-10 minutes. Dispense adhesive and cure at recommended schedules.

AVAILABILITY:

2 parts Kit - Packaged in 4 OZ, 8 OZ and 1 lb. container. **Premixed and frozen** - Packaged in 3cc, 5cc and 10cc disposable syringes.

FOR INDUSTRIAL USE ONLY:

Practices of good housekeeping, safety and cleanliness should be followed before, during and after use.

WARNING!

Adequate ventilation of work place and ovens is essential. These materials may cause injury to the skin following prolonged or repeated contact and dermatitis in susceptible individuals. In case of skin contact, wash thoroughly with soap and water. For eyes, flush immediately with plenty of water for at least 10 minutes and seek medical attention. Refer to Material Safety Data Sheet (MSDS) for additional health and safety information.